



CURVES

PH100-Si-HA Sensitivity



PH100-Si-HA Maximum Power



DISPLAYS & PC INTERFACES

ENERGY DETECTORS

POWER DETECTORS

HIGH POWER SOLUTIONS

PHOTODETECTORS

THZ DETECTORS


OEM DETECTORS

SPECIAL PRODUCTS


BEAM DIAGNOSTICS

CURVES

PH100-SiUV Sensitivity




PH100-SiUV Maximum Power




CURVES

PH20-Ge Sensitivity




PH20-Ge Maximum Power




CURVES

PE10B-Si Sensitivity




PE10B-Si Maximum Energy




CURVES

PE5B-Ge Sensitivity



PE5B-Ge Maximum Energy



DISPLAYS &
PC INTERFACES

ENERGY DETECTORS

POWER DETECTORS

HIGH-POWER SOLUTIONS

PHOTODETECTORS

THZ DETECTORS


OEM DETECTORS

SPECIAL PRODUCTS

BEAM DIAGNOSTICS

CURVES

Pronto-Si Sensitivity



Pronto-Si Maximum Power

